

Type number	Package	Package description	Total product weight
74AHCT125PW	SOT402-1	TSSOP14	51.79255 mg

12NC	Version	Pb-free soldering			Pb soldering			Number of processing cycles	Assembly site	RHF-indicator
		MSL	PPT	MPPT	MSL	PPT	MPPT			
935262765118	18	1	260	30 s	1	240	20 s	3	Suzhou, China; Nijmegen, Netherlands; Bangkok, Thailand	

Subpart	Material group	Substances	CAS number	Mass(mg)	Mass(%) of subpart	Mass(%) of total product
Adhesive	Filler	Silver (Ag)	7440-22-4	0.03114	77.86000	0.06013
		Polymer	Acrylic resin	Proprietary	0.00607	15.18000
		Resin system	Proprietary	0.00278	6.96000	0.00538
		subTotal		0.04000	100.00000	0.07723
Die	Doped silicon	Silicon (Si)	7440-21-3	0.15110	100.00000	0.29175
		subTotal		0.15110	100.00000	0.29175
Lead Frame Material	Copper alloy	Copper (Cu)	7440-50-8	19.04564	97.47000	36.77293
		Iron (Fe)	7439-89-6	0.46896	2.40000	0.90546
		Phosphorous (P)	7723-14-0	0.00586	0.03000	0.01132
		Zinc (Zn)	7440-66-6	0.01954	0.10000	0.03773
		subTotal		19.54000	100.00000	37.72744
Mould Compound	Additive	Non hazardous	Proprietary	1.48896	4.70000	2.87485
	Filler	Silica fused	60676-86-0	25.02720	79.00000	48.32201
	Flame retardant	Magnesium Hydroxide (Mg(OH)2)	1309-42-8	1.90080	6.00000	3.67003
	Pigment	Carbon black	1333-86-4	0.06336	0.20000	0.12233
	Polymer	1.4-bis(methoxymethyl)benzene/phenol copolymer	26834-02-6	1.26720	4.00000	2.44668
		Non hazardous	Proprietary	1.29888	4.10000	2.50785
		Tetramethylbiphenyl diglycidyl ether	85954-11-6	0.63360	2.00000	1.22334
	subTotal		31.68000	100.00000	61.16709	
Pre-Plating	Pure metal layer	Gold (Au)	7440-57-5	0.00290	1.00000	0.00560
		Nickel (Ni) - cas no. 7440-02-0	7440-02-0	0.28130	97.00000	0.54313
		Palladium (Pd)	7440-05-3	0.00580	2.00000	0.01120
		subTotal		0.29000	100.00000	0.55993
Wire	Pure metal	Copper (Cu)	7440-50-8	0.09145	100.00000	0.17657
		subTotal		0.09145	100.00000	0.17657

## Disclaimer

All information in this document is furnished for exploratory or indicative purposes only. All information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia may make changes to information published in this document at any time and without notice. Minor deviations may occur in the products from different manufacturing location. This document supersedes and replaces all information supplied prior to the publication hereof. Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.